

MONOFOKAL

# DRIVEVISIONES



## Ciljna grupa

Preporučuje se vozačima koji žele jasan i precizan vid, pogotovo tokom noćne vožnje.

## Tehnologija

IOT Endless Drive SV

## Način izrade

Unutrašnja izrada monofokalne površine.

## Poručivanje dioptrija

1/4, 1/8, 1/100

## Individualni parametri


IPD, Vertex, Panto, Ztilt

## Optimizacija

Specijalno tanjenje za sočivo u plus opsegu na osnovu oblika okvira i parametra za fitovanje sočiva u okvir. Ukoliko se sočivo poručuje bez opcije Optimizacija, topografija sočiva će biti decentrirana nazalno u odnosu na geometrijski centar za 2,5 mm.

## Oznake na sočivima

- gravure
- markeri



## MATERIJALI

1.50 CR-39	1
1.53 Trivex	2
1.59 Poly	4
1.60 High Index	5
1.60 Tribrid	6
1.67 High Index	7
1.74 High Index	8

## DORADE

Bez dorade	W	Transitions GEN 8 Sapphire	F	Nupolar Gray	S
Remuve 400	H	Transitions GEN 8 Amethyst	M	Nupolar Gray Light	L
Remuve 420	R	Transitions GEN 8 Amber	A	Nupolar Green	E
Remuve 420 Photomatic Brown	O	Transitions GEN 8 Emerald	E	Transitions XTRActive Polarised Gray	X
Remuve 420 Photomatic Gray	U	Transitions XTRActive Brown	C	DriveWear	D
Transitions GEN 8 Brown	Z	Transitions XTRActive Gray	L		
Transitions GEN 8 Gray	N	Transitions XTRActive Green	K		
Transitions GEN 8 Green	V	Nupolar Brown	B		