

PROGRESIV

# INFINI XL



### Ciljna grupa

Iskusni poznavaooci progresivnih sočiva. Starosna dob 45+.

### Tehnologija

OPTOTECH Extended IXL

### Način izrade

Unutrašnja izrada progresivne površine.

### Poručivanje dioptrija

1/4

### Individualni parametri

IPD, PL, Vertex, Panto, Ztilt, NVD

### Inset

Po potrebi od 0 do 4 ili automatski izračun inseta.

### Progresivna dužina

15 mm, 16 mm, 17 mm, 18 mm, 19 mm ili varijabilna u odnosu na visinu fitovanja.

### Minimalna visina ugradnje

17 mm, 18 mm, 19 mm, 20 mm, 21 mm

### Optimizacija

Specijalno tanjenje za sočivo u plus opsegu na osnovu oblika okvira i parametra za fitovanje sočiva u okvir. Ukoliko se sočivo poručuje bez opcije Optimizacija, topografija sočiva će biti decentrirana nazalno u odnosu na geometrijski centar za 2,5 mm.

### Ocene korisnika

Vid – daljina



Vid – blizina



Spontano privikavanje



Vid – srednja daljina



Komfor pri korištenju




Korištenje digitalnih uređaja



### Oznake na sočivima

- gravure
- markeri



### MATERIJALI

1.50 CR-39	1
1.53 Trivex	2
1.56 Mid. index	3
1.59 Poly	4
1.60 High Index	5
1.60 Tribrid	6
1.67 High Index	7
1.74 High Index	8

### DORADE

Bez dorade	W	Transitions GEN 8 Sapphire	F	Nupolar Gray	S
Remuve 400	H	Transitions GEN 8 Amethyst	M	Nupolar Gray Light	L
Remuve 420	R	Transitions GEN 8 Amber	A	Nupolar Green	E
Remuve 420 Photomatic Brown	O	Transitions GEN 8 Emerald	E	Transitions XTRActive Polarised Gray	X
Remuve 420 Photomatic Gray	U	Transitions XTRActive Brown	C	Photomatic Brown	B
Transitions GEN 8 Brown	Z	Transitions XTRActive Gray	L	Photomatic Gray	I
Transitions GEN 8 Gray	N	Transitions XTRActive Green	K	DriveWear	D
Transitions GEN 8 Green	V	Nupolar Brown	B		