

MONOFOKAL

LIGHTFORM2.0



Ciljna grupa

Monofokalno sočivo sa blago pojačanim dodatkom u donjem delu sočiva. Preporučuje se kategoriji ljudi koji osećaju napor u očima, tenziju kao i glavobolju usled dužeg rada sa digitalnim uređajima.

Dizajn 0.40 – starosna dob 20+
Dizajn 0.60 – starosna dob 35+
Dizajn 0.80 – starosna dob 43+

Tehnologija

IOT Endless Anti-fatigue SV

Način izrade

Unutrašnja izrada monofokalne površine.

Poručivanje dioptrija

1/4, 1/8, 1/100

Individualni parametri

IPD, Vertex, Panto, Ztilt

Minimalna visina ugradnje

16 mm

Optimizacija

Specijalno tanjenje za sočivo u plus opsegu na osnovu oblika okvira i parametra za fitovanje sočiva u okvir. Ukoliko se sočivo poručuje bez opcije Optimizacija, topografija sočiva će biti decentrirana nazalno u odnosu na geometrijski centar za 2,5 mm.

Ocene korisnika

Vid – daljina



Vid – blizina



Spontano privikavanje



Vid – srednja daljina



Komfor pri korištenju




Korištenje digitalnih uređaja



Oznake na sočivima

- gravure
- markeri



MATERIJALI

1.50 CR-39	1
1.53 Trivex	2
1.59 Poly	4
1.60 High Index	5
1.60 Tribrid	6
1.67 High Index	7
1.74 High Index	8

DORADE

Bez dorade	W	Transitions GEN 8 Sapphire	F	Nupolar Gray	S
Remuve 400	H	Transitions GEN 8 Amethyst	M	Nupolar Gray Light	L
Remuve 420	R	Transitions GEN 8 Amber	A	Nupolar Green	E
Remuve 420 Photomatic Brown	O	Transitions GEN 8 Emerald	E	Transitions XTRActive Polarised Gray	X
Remuve 420 Photomatic Gray	U	Transitions XTRActive Brown	C	DriveWear	D
Transitions GEN 8 Brown	Z	Transitions XTRActive Gray	L		
Transitions GEN 8 Gray	N	Transitions XTRActive Green	K		
Transitions GEN 8 Green	V	Nupolar Brown	B		